

This Full Body Harness with Belt is suitable for use as part of a personal fall protection system providing various attachment points for a user to connect their fall protection connecting system. This product is only to be used by a competent person. Inspect this product before use as per the supplied instruction. This equipment shall be removed from service if it fails an inspection or is involved in a fall.

Product Code	Description	Size
DP_WAUHAR14GT	Base Full Body Fall Arrest Harness with Belt	Small, Medium, Large
DP_WAUHAR14XX	Base Full Body Fall Arrest Harness with Belt	XLarge, XXLarge

Standard

- ▲ Certified to AS/NZS1891.1:2020.

User Rating

- ▲ Rated for users up to the single user limit of the connecting system (AS/NZS1891.5 Lanyard, AS/NZS1891.3 Fall Arrest Device).

Material Specification

- ▲ Webbing & Thread: Polyester.
- ▲ Buckles: Zinc plated steel.
- ▲ Label: Vinyl.
- ▲ Label Pack: Nylon.



Description

- ▲ Two (2) fall arrest anchorage points (back/front).
- ▲ Visual fall indicator for easy inspection.
- ▲ Four (4) locations for parking unused lanyard legs.
- ▲ Ideal for construction and maintenance.
- ▲ Three (3) adjustment locations, including three (3) pass thru buckles.
- ▲ Comfort waist belt with work positioning side waist attachment points (pole strap use).



www.safetylink.com



Catalogue



Safety Centre
Training

	ATTACHMENTS					ADJUSTMENT			
PRODUCT CODE	STERNAL	DORSAL	BELT / SIDE	D-RINGS	REAR WAIST	LEGS	TORSO	CHEST	WEIGHT (kg)
WAUHAR14	Loops	D-Ring	D-Rings	N/a		Pass Thru	N/A	Clip	1.10

Always consult the instructions provided by the manufacturer of each component of your fall arrest system to accurately assess Fall Clearance.

© 2018, SafetyLink Pty Ltd, Australia.

Patents: SafetyLink Pty Ltd has a multitude of patents, patents pending, design applications, trademarks and copyrighted documents both lodged and issued. Should you wish to know the progress of our intellectual property on a specific product please email us on ip@safetylink.com and quote the product code.

Doc ID: MKT-7876 Version: 3.0